

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744713

Luminaire Tested: LD4D20D010-EU4DR6520359050-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR6520359050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1914.5 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744713
CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P744713

CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101529
5°	101272
10°	101186
15°	98067
20°	89275
25°	77800
30°	64708
35°	51270
40°	37000
45°	23375
50°	12184
55°	6476
60°	3399
65°	1866
70°	786
75°	857
80°	605
85°	469

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23375 cd/sqm



TEST NUMBER: P744713

CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	8.6
10°-20°	450.2	23.5
20°-30°	550.3	28.7
30°-40°	446.5	23.3
40°-50°	222.5	11.6
50°-60°	62.1	3.2
60°-70°	14.1	0.7
70°-80°	3.7	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.8	60.8
0°-40°	1611.3	84.2
0°-60°	1895.8	99.0
0°-90°	1914.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1914.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1738	
5°	1727	164
15°	1622	450
25°	1207	550
35°	719	446
45°	283	222
55°	64	62
65°	14	14
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P744713

CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1738.4
2.5°	1737.1
5°	1727.4
7.5°	1721.8
10°	1706.2
12.5°	1674.5
15°	1621.9
17.5°	1539.6
20°	1436.4
22.5°	1325.1
25°	1207.3
27.5°	1081.3
30°	959.5
32.5°	839.1
35°	719.1
37.5°	599.3
40°	485.3
42.5°	378.6
45°	283.0
47.5°	197.2
50°	134.1
52.5°	92.5
55°	63.6
57.5°	42.9
60°	29.1
62.5°	20.2
65°	13.5
67.5°	6.9
70°	4.6
72.5°	4.4
75°	3.8
77.5°	2.6
80°	1.8
82.5°	1.3
85°	0.7
87.5°	0.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)