

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746606

Luminaire Tested: LD4D30D010-EU4DR7020359027-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P746606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR7020359027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2618.2 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746606
CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P746606

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	321609
5°	312056
10°	303360
15°	299382
20°	279555
25°	210020
30°	148469
35°	52579
40°	27656
45°	29451
50°	30494
55°	31069
60°	31270
65°	30610
70°	28879
75°	26764
80°	23784
85°	19306

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 31275 cd/sqm



TEST NUMBER: P746606

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.4	10.3
10°-20°	736.1	28.1
20°-30°	810.7	31.0
30°-40°	309.7	11.8
40°-50°	146.3	5.6
50°-60°	145.4	5.6
60°-70°	116.4	4.4
70°-80°	66.9	2.6
80°-90°	18.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1815.2	69.3
0°-40°	2125.0	81.2
0°-60°	2416.6	92.3
0°-90°	2618.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2618.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2944	
5°	2845	268
15°	2647	736
25°	1742	811
35°	394	310
45°	191	146
55°	163	145
65°	118	116
75°	63	67
85°	15	18
90°	0	



TEST NUMBER: P746606

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2943.5
2.5°	2912.8
5°	2845.2
7.5°	2788.8
10°	2734.3
12.5°	2688.2
15°	2646.7
17.5°	2546.5
20°	2404.3
22.5°	2097.7
25°	1742.1
27.5°	1516.5
30°	1176.8
32.5°	760.1
35°	394.2
37.5°	213.0
40°	193.9
42.5°	192.5
45°	190.6
47.5°	186.4
50°	179.4
52.5°	171.5
55°	163.1
57.5°	153.8
60°	143.1
62.5°	131.0
65°	118.4
67.5°	104.4
70°	90.4
72.5°	76.4
75°	63.4
77.5°	49.8
80°	37.8
82.5°	26.6
85°	15.4
87.5°	6.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)