

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738839

Luminaire Tested: LD4D02D010-EU4DR150210IC9027-4LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P738839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR150210IC9027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 357.9 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P738839

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P738839

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	548726	548726	548726
5°	322458	318281	320802
10°	96237	96909	98393
15°	23938	24407	23651
20°	7159	8297	7315
25°	2524	3217	2555
30°	929	1221	944
35°	465	523	450
40°	291	320	291
45°	217	231	217
50°	174	174	174
55°	146	146	146
60°	119	119	119
65°	86	86	86
70°	73	73	73
75°	45	45	60
80°	32	32	32
85°	17	17	17

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 231 cd/sqm



TEST NUMBER: P738839

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	64.9
10°-20°	95.5	26.7
20°-30°	19.0	5.3
30°-40°	4.7	1.3
40°-50°	2.5	0.7
50°-60°	1.9	0.5
60°-70°	1.3	0.4
70°-80°	0.7	0.2
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.6	96.8
0°-40°	351.3	98.2
0°-60°	355.7	99.4
0°-90°	357.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4877	4877	4877	4877	4877	
5°	3173	3140	3132	3154	3157	232
15°	276	281	281	276	272	94
25°	32	37	41	36	33	17
35°	6	7	7	7	6	4
45°	3	3	3	3	3	2
55°	2	2	2	2	2	2
65°	1	1	1	1	1	1
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P738839

CATALOG NUMBER: LD4D02D010-EU4DR150210IC9027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4876.7	4876.7	4876.7	4876.7	4876.7
2.5°	4398.9	4402.7	4404.1	4408.4	4424.5
5°	3172.9	3140.2	3131.8	3153.5	3156.6
7.5°	1879.5	1886.1	1910.2	1915.6	1896.2
10°	1031.4	1039.9	1038.6	1046.1	1054.5
12.5°	527.5	520.9	518.8	527.3	515.5
15°	275.6	280.8	281.0	276.0	272.3
17.5°	148.2	154.2	164.1	156.1	143.7
20°	87.5	92.9	101.4	94.8	89.4
22.5°	54.1	58.4	64.4	59.2	54.9
25°	32.4	36.7	41.3	36.5	32.8
27.5°	19.2	22.9	25.8	22.7	19.0
30°	12.4	14.5	16.3	14.2	12.6
32.5°	8.7	9.5	10.3	9.5	8.7
35°	6.4	6.8	7.2	6.8	6.2
37.5°	5.0	5.4	5.6	5.2	4.7
40°	4.1	4.3	4.5	4.3	4.1
42.5°	3.5	3.7	3.7	3.7	3.5
45°	3.1	3.1	3.3	3.1	3.1
47.5°	2.7	2.7	2.9	2.7	2.7
50°	2.5	2.5	2.5	2.5	2.5
52.5°	2.3	2.3	2.3	2.3	2.3
55°	2.1	2.1	2.1	2.1	2.1
57.5°	1.9	1.9	1.9	1.9	1.9
60°	1.7	1.7	1.7	1.7	1.7
62.5°	1.4	1.4	1.4	1.4	1.4
65°	1.2	1.2	1.2	1.2	1.2
67.5°	1.2	1.2	1.2	1.2	1.2
70°	1.0	1.0	1.0	1.0	1.0
72.5°	0.8	0.8	0.8	0.8	0.8
75°	0.6	0.6	0.6	0.6	0.8
77.5°	0.6	0.6	0.6	0.6	0.6
80°	0.4	0.4	0.4	0.4	0.4
82.5°	0.4	0.4	0.4	0.4	0.4
85°	0.2	0.2	0.2	0.2	0.2
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)