

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739085

Luminaire Tested: LD4D02D010-EU4DR300210IC9030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR300210IC9030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 340.3 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739085

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P739085

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	83761	83761	83761
5°	81361	81269	81361
10°	70465	69975	70457
15°	45977	45731	45502
20°	22865	23720	22832
25°	11520	12989	11283
30°	4614	5020	4013
35°	2140	2046	1719
40°	919	1029	869
45°	649	801	660
50°	226	583	238
55°	133	240	133
60°	92	107	92
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 801 cd/sqm



TEST NUMBER: P739085

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	28.3
10°-20°	155.0	45.5
20°-30°	67.0	19.7
30°-40°	15.3	4.5
40°-50°	5.2	1.5
50°-60°	1.3	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	318.2	93.5
0°-40°	333.4	98.0
0°-60°	339.9	99.9
0°-90°	340.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	340.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1094	1094	1094	1094	1094	
5°	1059	1058	1058	1060	1059	96
15°	580	573	577	575	574	155
25°	136	142	154	138	134	65
35°	23	23	22	22	18	16
45°	6	7	7	7	6	4
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P739085

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1094.3	1094.3	1094.3	1094.3	1094.3
2.5°	1087.1	1086.3	1086.8	1087.3	1087.5
5°	1058.9	1057.8	1057.7	1059.8	1058.9
7.5°	1002.0	1000.5	998.3	1003.3	1008.0
10°	906.6	905.0	900.3	902.6	906.5
12.5°	765.9	760.8	760.6	768.2	767.1
15°	580.2	573.2	577.1	575.2	574.2
17.5°	390.2	387.5	392.6	391.1	384.4
20°	280.7	281.4	291.2	286.2	280.3
22.5°	204.8	207.4	219.0	206.3	201.6
25°	136.4	141.5	153.8	137.9	133.6
27.5°	83.9	86.2	98.7	82.8	80.4
30°	52.2	51.0	56.8	48.8	45.4
32.5°	34.2	32.7	34.6	31.1	28.4
35°	22.9	23.4	21.9	21.8	18.4
37.5°	14.3	16.4	14.5	15.5	11.8
40°	9.2	11.9	10.3	11.3	8.7
42.5°	7.6	9.2	8.4	9.0	7.7
45°	6.0	7.4	7.4	7.4	6.1
47.5°	3.3	5.0	6.4	5.1	3.6
50°	1.9	2.5	4.9	2.6	2.0
52.5°	1.3	1.4	3.4	1.5	1.3
55°	1.0	1.0	1.8	1.1	1.0
57.5°	0.7	0.8	1.0	0.8	0.7
60°	0.6	0.6	0.7	0.6	0.6
62.5°	0.5	0.5	0.5	0.5	0.5
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)