

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745865

Luminaire Tested: LD4D30D010-EU4DR2015309040-4LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR2015309040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3078.8 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745865
CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P745865

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	90	89	88																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	85																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	83																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	81																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	79																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	77																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	75																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	73																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1914685
5°	1727408
10°	969515
15°	492820
20°	208652
25°	96324
30°	50995
35°	27477
40°	14691
45°	8684
50°	5031
55°	2667
60°	1704
65°	1215
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8684 cd/sqm



TEST NUMBER: P745865

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1247.7	40.5
10°-20°	1228.6	39.9
20°-30°	401.4	13.0
30°-40°	136.7	4.4
40°-50°	45.9	1.5
50°-60°	13.8	0.4
60°-70°	4.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2877.6	93.5
0°-40°	3014.3	97.9
0°-60°	3074.0	99.8
0°-90°	3078.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3078.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17524	
5°	15750	###
15°	4357	1229
25°	799	401
35°	206	137
45°	56	46
55°	14	14
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745865

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	17524.0
0.5°	17524.0
1°	17502.2
1.5°	17458.5
2°	17378.9
2.5°	17272.8
3°	17123.0
3.5°	16913.9
4°	16603.4
4.5°	16225.7
5°	15749.8
5.5°	15124.0
6°	14482.7
6.5°	13747.7
7°	13028.3
7.5°	12185.7
8°	11433.5
8.5°	10676.7
9°	9977.6
9.5°	9336.3
10°	8738.6
12.5°	6274.6
15°	4356.8
17.5°	2846.3
20°	1794.5
22.5°	1162.5
25°	799.0
27.5°	561.8
30°	404.2
32.5°	290.2
35°	206.0
37.5°	143.6
40°	103.0
42.5°	74.9
45°	56.2
47.5°	43.7
50°	29.6
52.5°	18.7
55°	14.0
57.5°	10.9
60°	7.8
62.5°	6.2
65°	4.7



TEST NUMBER: P745865
CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.1
70°		1.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)