

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739709

Luminaire Tested: LD4D02D010-EU4DR700210IC9030-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P739709  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D02D010-EU4DR700210IC9030-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 351.8 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P739709

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P739709

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	43213
5°	41930
10°	40762
15°	40224
20°	37568
25°	28222
30°	19946
35°	7069
40°	3723
45°	3956
50°	4097
55°	4172
60°	4217
65°	4111
70°	3865
75°	3588
80°	3209
85°	2633

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 4217 cd/sqm



TEST NUMBER: P739709

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.1	10.2
10°-20°	98.9	28.1
20°-30°	108.9	31.0
30°-40°	41.6	11.8
40°-50°	19.6	5.6
50°-60°	19.5	5.6
60°-70°	15.6	4.4
70°-80°	9.0	2.6
80°-90°	2.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	243.9	69.3
0°-40°	285.5	81.2
0°-60°	324.7	92.3
0°-90°	351.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	351.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	396	
5°	382	36
15°	356	99
25°	234	109
35°	53	42
45°	26	20
55°	22	20
65°	16	16
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P739709

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	395.5
2.5°	391.4
5°	382.3
7.5°	374.7
10°	367.4
12.5°	361.2
15°	355.6
17.5°	342.2
20°	323.1
22.5°	281.8
25°	234.1
27.5°	203.7
30°	158.1
32.5°	102.2
35°	53.0
37.5°	28.6
40°	26.1
42.5°	25.8
45°	25.6
47.5°	25.0
50°	24.1
52.5°	23.0
55°	21.9
57.5°	20.7
60°	19.3
62.5°	17.6
65°	15.9
67.5°	14.0
70°	12.1
72.5°	10.3
75°	8.5
77.5°	6.7
80°	5.1
82.5°	3.6
85°	2.1
87.5°	0.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)