

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746658

Luminaire Tested: LD4D30D010-EU4DR7020359050-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746658  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR7020359050-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2898.3 lumens  
Efficiency: N/A  
Efficacy: 99.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746658  
CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P746658

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	356015
5°	345442
10°	335812
15°	331404
20°	309460
25°	232480
30°	164353
35°	58222
40°	30608
45°	32603
50°	33758
55°	34403
60°	34614
65°	33868
70°	31978
75°	29635
80°	26301
85°	21312

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 34614 cd/sqm



TEST NUMBER: P746658

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	297.1	10.3
10°-20°	814.9	28.1
20°-30°	897.4	31.0
30°-40°	342.9	11.8
40°-50°	161.9	5.6
50°-60°	161.0	5.6
60°-70°	128.9	4.4
70°-80°	74.1	2.6
80°-90°	20.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2009.4	69.3
0°-40°	2352.3	81.2
0°-60°	2675.2	92.3
0°-90°	2898.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2898.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3258	
5°	3150	297
15°	2930	815
25°	1928	897
35°	436	343
45°	211	162
55°	181	161
65°	131	129
75°	70	74
85°	17	20
90°	0	



TEST NUMBER: P746658

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3258.4
2.5°	3224.4
5°	3149.6
7.5°	3087.2
10°	3026.8
12.5°	2975.7
15°	2929.8
17.5°	2818.9
20°	2661.5
22.5°	2322.1
25°	1928.4
27.5°	1678.7
30°	1302.7
32.5°	841.4
35°	436.5
37.5°	235.8
40°	214.6
42.5°	213.1
45°	211.0
47.5°	206.4
50°	198.6
52.5°	189.9
55°	180.6
57.5°	170.2
60°	158.4
62.5°	145.0
65°	131.0
67.5°	115.6
70°	100.1
72.5°	84.6
75°	70.2
77.5°	55.2
80°	41.8
82.5°	29.4
85°	17.0
87.5°	6.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)