

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738960

Luminaire Tested: LD4D02D010-EU4DR200210IC9040-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P738960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR200210IC9040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 442.8 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P738960
CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P738960

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87																
	2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91	90	89	88	87	86	85	84																
	3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	90	89	88	87	86	85	84	83	82	81																
	4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78																
	5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	82	81	80	79	78	77	76	75																
	6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	80	79	78	77	76	75	74	73																
	7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	78	77	76	75	74	73	72	71																
	8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	76	75	74	73	72	71	70	69																
	9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	74	73	72	71	70	69	68	67																
	10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	72	71	70	69	68	67	66	65																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275392
5°	248454
10°	139448
15°	70878
20°	30010
25°	13852
30°	7330
35°	3948
40°	2111
45°	1252
50°	731
55°	381
60°	240
65°	181
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1252 cd/sqm



TEST NUMBER: P738960

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.5	40.5
10°-20°	176.7	39.9
20°-30°	57.7	13.0
30°-40°	19.6	4.4
40°-50°	6.6	1.5
50°-60°	2.0	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.9	93.5
0°-40°	433.5	97.9
0°-60°	442.1	99.8
0°-90°	442.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	442.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2520	
5°	2265	179
15°	627	177
25°	115	58
35°	30	20
45°	8	7
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P738960

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2520.5
0.5°	2520.5
1°	2517.3
1.5°	2511.0
2°	2499.6
2.5°	2484.3
3°	2462.8
3.5°	2432.7
4°	2388.0
4.5°	2333.7
5°	2265.3
5.5°	2175.3
6°	2083.0
6.5°	1977.3
7°	1873.8
7.5°	1752.6
8°	1644.5
8.5°	1535.6
9°	1435.1
9.5°	1342.8
10°	1256.9
12.5°	902.5
15°	626.6
17.5°	409.4
20°	258.1
22.5°	167.2
25°	114.9
27.5°	80.8
30°	58.1
32.5°	41.7
35°	29.6
37.5°	20.6
40°	14.8
42.5°	10.8
45°	8.1
47.5°	6.3
50°	4.3
52.5°	2.7
55°	2.0
57.5°	1.6
60°	1.1
62.5°	0.9
65°	0.7



TEST NUMBER: P738960
CATALOG NUMBER: LD4D02D010-EU4DR200210IC9040-4LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)