

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747218

Luminaire Tested: LD4D35BD010-EU4DR6020359024-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6020359024-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2883.4 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P747218

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P747218

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	374153
5°	383347
10°	387979
15°	369603
20°	325878
25°	263583
30°	178294
35°	89340
40°	14491
45°	14185
50°	14465
55°	14687
60°	15100
65°	15434
70°	15813
75°	16000
80°	15416
85°	12787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 16000 cd/sqm



TEST NUMBER: P747218

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.1	11.6
10°-20°	903.8	31.3
20°-30°	972.4	33.7
30°-40°	422.7	14.7
40°-50°	71.0	2.5
50°-60°	69.0	2.4
60°-70°	59.0	2.0
70°-80°	39.5	1.4
80°-90°	11.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2210.3	76.7
0°-40°	2633.0	91.3
0°-60°	2773.0	96.2
0°-90°	2883.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2883.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3424	
5°	3495	334
15°	3268	904
25°	2186	972
35°	670	423
45°	92	71
55°	77	69
65°	60	59
75°	38	40
85°	10	12
90°	0	



TEST NUMBER: P747218

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3424.4
2.5°	3520.6
5°	3495.2
7.5°	3503.3
10°	3497.0
12.5°	3424.8
15°	3267.5
17.5°	3056.3
20°	2802.7
22.5°	2531.3
25°	2186.4
27.5°	1748.7
30°	1413.2
32.5°	1089.2
35°	669.8
37.5°	286.6
40°	101.6
42.5°	93.6
45°	91.8
47.5°	88.7
50°	85.1
52.5°	81.1
55°	77.1
57.5°	73.1
60°	69.1
62.5°	64.6
65°	59.7
67.5°	54.8
70°	49.5
72.5°	43.7
75°	37.9
77.5°	31.2
80°	24.5
82.5°	17.4
85°	10.2
87.5°	3.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)