

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P738968

Luminaire Tested: LD4D02D010-EU4DR200210IC9050-4LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P738968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR200210IC9050-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 395.9 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P738968

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9050-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P738968

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9050-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94	92	91	89	88	86	85																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	92	91	89	88	86	85	83	82	81																	
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	89	88	86	85	83	82	81	79	77																		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	83	82	81	79	77	75																			
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	83	82	81	79	77	75	73																				
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	81	80	79	77	75	73	71																				
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	79	77	75	73	71	69																					
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	77	75	73	71	69	67																					
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	75	73	71	69	67	65																					
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	73	71	69	67	65	63																					

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246219
5°	222142
10°	124670
15°	63378
20°	26836
25°	12381
30°	6560
35°	3535
40°	1883
45°	1113
50°	646
55°	343
60°	219
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1113 cd/sqm



TEST NUMBER: P738968

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9050-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.4	40.5
10°-20°	158.0	39.9
20°-30°	51.6	13.0
30°-40°	17.6	4.4
40°-50°	5.9	1.5
50°-60°	1.8	0.4
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.0	93.5
0°-40°	387.6	97.9
0°-60°	395.3	99.8
0°-90°	395.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	395.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2254	
5°	2025	160
15°	560	158
25°	103	52
35°	26	18
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P738968

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9050-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2253.5
0.5°	2253.5
1°	2250.7
1.5°	2245.1
2°	2234.9
2.5°	2221.2
3°	2201.9
3.5°	2175.1
4°	2135.1
4.5°	2086.6
5°	2025.4
5.5°	1944.9
6°	1862.4
6.5°	1767.9
7°	1675.4
7.5°	1567.0
8°	1470.3
8.5°	1373.0
9°	1283.1
9.5°	1200.6
10°	1123.7
12.5°	806.9
15°	560.3
17.5°	366.0
20°	230.8
22.5°	149.5
25°	102.7
27.5°	72.2
30°	52.0
32.5°	37.3
35°	26.5
37.5°	18.5
40°	13.2
42.5°	9.6
45°	7.2
47.5°	5.6
50°	3.8
52.5°	2.4
55°	1.8
57.5°	1.4
60°	1.0
62.5°	0.8
65°	0.6



TEST NUMBER: P738968

CATALOG NUMBER: LD4D02D010-EU4DR200210IC9050-4LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)