

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747373

Luminaire Tested: LD4D35BD010-EU4DR7020359024-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747373  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR7020359024-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2764.1 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P747373  
CATALOG NUMBER: LD4D35BD010-EU4DR7020359024-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P747373

CATALOG NUMBER: LD4D35BD010-EU4DR7020359024-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	339539
5°	329451
10°	320269
15°	316066
20°	295147
25°	221726
30°	156745
35°	55527
40°	29196
45°	31089
50°	32194
55°	32802
60°	33019
65°	32317
70°	30508
75°	28242
80°	25105
85°	20309

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 33024 cd/sqm



TEST NUMBER: P747373

CATALOG NUMBER: LD4D35BD010-EU4DR7020359024-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	283.3	10.3
10°-20°	777.1	28.1
20°-30°	855.9	31.0
30°-40°	327.0	11.8
40°-50°	154.4	5.6
50°-60°	153.5	5.6
60°-70°	122.9	4.4
70°-80°	70.6	2.6
80°-90°	19.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1916.4	69.3
0°-40°	2243.4	81.2
0°-60°	2551.4	92.3
0°-90°	2764.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2764.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3108	
5°	3004	283
15°	2794	777
25°	1839	856
35°	416	327
45°	201	154
55°	172	154
65°	125	123
75°	67	71
85°	16	19
90°	0	



TEST NUMBER: P747373

CATALOG NUMBER: LD4D35BD010-EU4DR7020359024-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3107.6
2.5°	3075.2
5°	3003.8
7.5°	2944.3
10°	2886.7
12.5°	2838.0
15°	2794.2
17.5°	2688.4
20°	2538.4
22.5°	2214.6
25°	1839.2
27.5°	1601.0
30°	1242.4
32.5°	802.5
35°	416.3
37.5°	224.9
40°	204.7
42.5°	203.2
45°	201.2
47.5°	196.8
50°	189.4
52.5°	181.1
55°	172.2
57.5°	162.4
60°	151.1
62.5°	138.3
65°	125.0
67.5°	110.2
70°	95.5
72.5°	80.7
75°	66.9
77.5°	52.6
80°	39.9
82.5°	28.0
85°	16.2
87.5°	6.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)