

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747308

Luminaire Tested: LD4D35BD010-EU4DR6520359027-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6520359027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2718.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P747308
CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P747308

CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	292393
5°	292632
10°	302939
15°	303442
20°	279369
25°	238038
30°	182218
35°	128741
40°	75993
45°	30857
50°	11185
55°	6229
60°	3584
65°	1965
70°	2076
75°	1604
80°	1699
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30857 cd/sqm



TEST NUMBER: P747308

CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	9.5
10°-20°	743.3	27.3
20°-30°	891.8	32.8
30°-40°	599.3	22.1
40°-50°	179.4	6.6
50°-60°	31.7	1.2
60°-70°	9.0	0.3
70°-80°	4.4	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1892.8	69.6
0°-40°	2492.2	91.7
0°-60°	2703.3	99.5
0°-90°	2718.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2718.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2676	
5°	2668	258
15°	2683	743
25°	1974	892
35°	965	599
45°	200	179
55°	33	32
65°	8	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P747308

CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2676.1
2.5°	2687.5
5°	2668.1
7.5°	2708.4
10°	2730.5
12.5°	2725.2
15°	2682.6
17.5°	2578.4
20°	2402.7
22.5°	2195.8
25°	1974.5
27.5°	1724.6
30°	1444.3
32.5°	1190.3
35°	965.2
37.5°	742.7
40°	532.8
42.5°	348.0
45°	199.7
47.5°	105.7
50°	65.8
52.5°	45.6
55°	32.7
57.5°	23.6
60°	16.4
62.5°	10.6
65°	7.6
67.5°	6.8
70°	6.5
72.5°	4.9
75°	3.8
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)