

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747386

Luminaire Tested: LD4D35BD010-EU4DR7020359027-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR7020359027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3131.0 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P747386
CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P747386

CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	384631
5°	373202
10°	362794
15°	358032
20°	334331
25°	251166
30°	177550
35°	62890
40°	33076
45°	35230
50°	36478
55°	37165
60°	37389
65°	36608
70°	34533
75°	31999
80°	28377
85°	23067

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 37396 cd/sqm



TEST NUMBER: P747386

CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	320.9	10.3
10°-20°	880.3	28.1
20°-30°	969.6	31.0
30°-40°	370.4	11.8
40°-50°	174.9	5.6
50°-60°	173.9	5.6
60°-70°	139.2	4.4
70°-80°	80.0	2.6
80°-90°	21.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2170.8	69.3
0°-40°	2541.3	81.2
0°-60°	2890.1	92.3
0°-90°	3131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3520	
5°	3403	321
15°	3165	880
25°	2083	970
35°	472	370
45°	228	175
55°	195	174
65°	142	139
75°	76	80
85°	18	22
90°	0	



TEST NUMBER: P747386

CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3520.3
2.5°	3483.5
5°	3402.7
7.5°	3335.2
10°	3270.0
12.5°	3214.8
15°	3165.2
17.5°	3045.4
20°	2875.4
22.5°	2508.7
25°	2083.4
27.5°	1813.6
30°	1407.3
32.5°	909.0
35°	471.5
37.5°	254.7
40°	231.9
42.5°	230.2
45°	228.0
47.5°	222.9
50°	214.6
52.5°	205.1
55°	195.1
57.5°	183.9
60°	171.1
62.5°	156.6
65°	141.6
67.5°	124.8
70°	108.1
72.5°	91.4
75°	75.8
77.5°	59.6
80°	45.1
82.5°	31.8
85°	18.4
87.5°	7.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)