

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745658

Luminaire Tested: LD4D25D010-EU4DR7020359024-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR7020359024-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2203.2 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')

CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745658
CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P745658

CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270661
5°	262613
10°	255298
15°	251941
20°	235267
25°	176747
30°	124940
35°	44256
40°	23277
45°	24785
50°	25667
55°	26154
60°	26310
65°	25750
70°	24311
75°	22501
80°	19946
85°	16172

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 26314 cd/sqm



TEST NUMBER: P745658

CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.8	10.3
10°-20°	619.5	28.1
20°-30°	682.3	31.0
30°-40°	260.7	11.8
40°-50°	123.1	5.6
50°-60°	122.4	5.6
60°-70°	98.0	4.4
70°-80°	56.3	2.6
80°-90°	15.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1527.6	69.3
0°-40°	1788.3	81.2
0°-60°	2033.7	92.3
0°-90°	2203.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2203.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2477	
5°	2394	226
15°	2227	619
25°	1466	682
35°	332	261
45°	160	123
55°	137	122
65°	100	98
75°	53	56
85°	13	15
90°	0	



TEST NUMBER: P745658

CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2477.2
2.5°	2451.3
5°	2394.4
7.5°	2347.0
10°	2301.1
12.5°	2262.2
15°	2227.3
17.5°	2143.0
20°	2023.4
22.5°	1765.3
25°	1466.1
27.5°	1276.2
30°	990.3
32.5°	639.7
35°	331.8
37.5°	179.2
40°	163.2
42.5°	162.0
45°	160.4
47.5°	156.9
50°	151.0
52.5°	144.3
55°	137.3
57.5°	129.4
60°	120.4
62.5°	110.2
65°	99.6
67.5°	87.8
70°	76.1
72.5°	64.3
75°	53.3
77.5°	41.9
80°	31.7
82.5°	22.3
85°	12.9
87.5°	5.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)