

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744889

Luminaire Tested: LD4D25D010-EU4DR2015309027-4LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR2015309027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2096.2 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744889
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P744889

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1303601
5°	1176100
10°	660086
15°	335533
20°	142062
25°	65582
30°	34720
35°	18700
40°	9998
45°	5903
50°	3434
55°	1829
60°	1158
65°	827
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5903 cd/sqm



TEST NUMBER: P744889

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	849.5	40.5
10°-20°	836.5	39.9
20°-30°	273.3	13.0
30°-40°	93.0	4.4
40°-50°	31.3	1.5
50°-60°	9.4	0.4
60°-70°	3.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1959.2	93.5
0°-40°	2052.2	97.9
0°-60°	2092.9	99.8
0°-90°	2096.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2096.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11931	
5°	10723	849
15°	2966	836
25°	544	273
35°	140	93
45°	38	31
55°	10	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744889

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	11931.1
0.5°	11931.1
1°	11916.3
1.5°	11886.5
2°	11832.3
2.5°	11760.1
3°	11658.1
3.5°	11515.7
4°	11304.3
4.5°	11047.2
5°	10723.2
5.5°	10297.1
6°	9860.5
6.5°	9360.1
7°	8870.3
7.5°	8296.6
8°	7784.5
8.5°	7269.2
9°	6793.2
9.5°	6356.5
10°	5949.6
12.5°	4272.1
15°	2966.3
17.5°	1937.9
20°	1221.8
22.5°	791.5
25°	544.0
27.5°	382.5
30°	275.2
32.5°	197.6
35°	140.2
37.5°	97.7
40°	70.1
42.5°	51.0
45°	38.2
47.5°	29.7
50°	20.2
52.5°	12.7
55°	9.6
57.5°	7.4
60°	5.3
62.5°	4.2
65°	3.2



TEST NUMBER: P744889
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.1
70°		1.1

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)