

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744890

Luminaire Tested: LD4D25D010-EU4DR2015309027-4LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR2015309027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2445.4 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744890
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P744890
 CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1520746
5°	1371996
10°	770045
15°	391423
20°	165724
25°	76505
30°	40498
35°	21821
40°	11667
45°	6892
50°	3995
55°	2133
60°	1355
65°	957
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6892 cd/sqm



TEST NUMBER: P744890

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	991.0	40.5
10°-20°	975.8	39.9
20°-30°	318.8	13.0
30°-40°	108.5	4.4
40°-50°	36.5	1.5
50°-60°	11.0	0.4
60°-70°	3.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2285.6	93.5
0°-40°	2394.1	97.9
0°-60°	2441.6	99.8
0°-90°	2445.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2445.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13918	
5°	12509	991
15°	3460	976
25°	635	319
35°	164	109
45°	45	36
55°	11	11
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744890
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13918.5
0.5°	13918.5
1°	13901.2
1.5°	13866.5
2°	13803.2
2.5°	13719.0
3°	13600.0
3.5°	13433.9
4°	13187.3
4.5°	12887.3
5°	12509.3
5.5°	12012.3
6°	11502.9
6.5°	10919.2
7°	10347.8
7.5°	9678.5
8°	9081.1
8.5°	8480.0
9°	7924.8
9.5°	7415.4
10°	6940.7
12.5°	4983.6
15°	3460.4
17.5°	2260.7
20°	1425.3
22.5°	923.4
25°	634.6
27.5°	446.2
30°	321.0
32.5°	230.5
35°	163.6
37.5°	114.0
40°	81.8
42.5°	59.5
45°	44.6
47.5°	34.7
50°	23.5
52.5°	14.9
55°	11.2
57.5°	8.7
60°	6.2
62.5°	5.0
65°	3.7



TEST NUMBER: P744890
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.5
70°		1.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)