

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747327

Luminaire Tested: LD4D35BD010-EU4DR6520359030-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P747327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6520359030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2800.8 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P747327

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P747327

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148527
5°	148150
10°	148025
15°	143463
20°	130606
25°	113810
30°	94657
35°	75005
40°	54131
45°	34203
50°	17827
55°	9480
60°	4976
65°	2736
70°	1144
75°	1264
80°	874
85°	737

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34203 cd/sqm



TEST NUMBER: P747327

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.5	8.6
10°-20°	658.6	23.5
20°-30°	805.0	28.7
30°-40°	653.1	23.3
40°-50°	325.5	11.6
50°-60°	90.8	3.2
60°-70°	20.6	0.7
70°-80°	5.4	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1704.0	60.8
0°-40°	2357.2	84.2
0°-60°	2773.5	99.0
0°-90°	2800.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2800.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2543	
5°	2527	240
15°	2373	659
25°	1766	805
35°	1052	653
45°	414	325
55°	93	91
65°	20	21
75°	6	5
85°	1	1
90°	0	



TEST NUMBER: P747327

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2543.1
2.5°	2541.2
5°	2527.0
7.5°	2518.8
10°	2496.0
12.5°	2449.7
15°	2372.7
17.5°	2252.3
20°	2101.4
22.5°	1938.4
25°	1766.1
27.5°	1581.9
30°	1403.6
32.5°	1227.6
35°	1052.0
37.5°	876.7
40°	710.0
42.5°	553.8
45°	414.1
47.5°	288.5
50°	196.2
52.5°	135.3
55°	93.1
57.5°	62.8
60°	42.6
62.5°	29.5
65°	19.8
67.5°	10.1
70°	6.7
72.5°	6.4
75°	5.6
77.5°	3.7
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)