

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744831

Luminaire Tested: LD4D25D010-EU4DR1515309030-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR1515309030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2406.5 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744831
CATALOG NUMBER: LD4D25D010-EU4DR1515309030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P744831

CATALOG NUMBER: LD4D25D010-EU4DR1515309030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3689315	3689315	3689315
5°	2168019	2139939	2156870
10°	647051	651586	661560
15°	160946	164081	159018
20°	48153	55762	49176
25°	16975	21625	17193
30°	6238	8214	6342
35°	3123	3529	3021
40°	1974	2166	1974
45°	1456	1554	1456
50°	1161	1161	1161
55°	968	968	968
60°	779	779	779
65°	592	592	592
70°	505	505	505
75°	317	317	423
80°	221	221	221
85°	116	116	116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 1554 cd/sqm



TEST NUMBER: P744831

CATALOG NUMBER: LD4D25D010-EU4DR1515309030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1560.8	64.9
10°-20°	642.0	26.7
20°-30°	127.5	5.3
30°-40°	31.8	1.3
40°-50°	16.7	0.7
50°-60°	12.4	0.5
60°-70°	8.7	0.4
70°-80°	5.0	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2330.3	96.8
0°-40°	2362.1	98.2
0°-60°	2391.3	99.4
0°-90°	2406.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2406.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	32788	32788	32788	32788	32788	
5°	21333	21113	21056	21202	21223	1558
15°	1853	1888	1889	1856	1831	635
25°	218	247	278	246	221	114
35°	43	46	49	46	42	29
45°	21	21	22	21	21	16
55°	14	14	14	14	14	12
65°	8	8	8	8	8	9
75°	4	4	4	4	6	5
85°	1	1	1	1	1	2
90°	0	0	0	0	0	



TEST NUMBER: P744831

CATALOG NUMBER: LD4D25D010-EU4DR1515309030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	32788.1	32788.1	32788.1	32788.1	32788.1
2.5°	29576.2	29601.2	29610.9	29640.0	29748.3
5°	21332.7	21113.3	21056.4	21202.2	21223.0
7.5°	12636.6	12681.1	12843.5	12879.5	12749.1
10°	6934.6	6991.5	6983.2	7033.2	7090.1
12.5°	3546.4	3502.0	3488.1	3545.0	3465.9
15°	1853.0	1887.7	1889.1	1855.8	1830.8
17.5°	996.6	1036.9	1103.5	1049.4	966.1
20°	588.5	624.6	681.5	637.1	601.0
22.5°	363.7	392.8	433.1	398.4	369.2
25°	217.9	247.1	277.6	245.7	220.7
27.5°	129.1	154.1	173.5	152.7	127.7
30°	83.3	97.2	109.7	95.8	84.7
32.5°	58.3	63.8	69.4	63.8	58.3
35°	43.0	45.8	48.6	45.8	41.6
37.5°	33.3	36.1	37.5	34.7	31.9
40°	27.8	29.1	30.5	29.1	27.8
42.5°	23.6	25.0	25.0	25.0	23.6
45°	20.8	20.8	22.2	20.8	20.8
47.5°	18.0	18.0	19.4	18.0	18.0
50°	16.7	16.7	16.7	16.7	16.7
52.5°	15.3	15.3	15.3	15.3	15.3
55°	13.9	13.9	13.9	13.9	13.9
57.5°	12.5	12.5	12.5	12.5	12.5
60°	11.1	11.1	11.1	11.1	11.1
62.5°	9.7	9.7	9.7	9.7	9.7
65°	8.3	8.3	8.3	8.3	8.3
67.5°	8.3	8.3	8.3	8.3	8.3
70°	6.9	6.9	6.9	6.9	6.9
72.5°	5.6	5.6	5.6	5.6	5.6
75°	4.2	4.2	4.2	4.2	5.6
77.5°	4.2	4.2	4.2	4.2	4.2
80°	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	2.8	2.8	2.8	2.8
85°	1.4	1.4	1.4	1.4	1.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)