

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745621

Luminaire Tested: LD4D25D010-EU4DR6520359035-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6520359035-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2154.2 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745621
CATALOG NUMBER: LD4D25D010-EU4DR6520359035-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P745621

CATALOG NUMBER: LD4D25D010-EU4DR6520359035-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114232
5°	113947
10°	113848
15°	110341
20°	100450
25°	87537
30°	72807
35°	57687
40°	41635
45°	26298
50°	13711
55°	7291
60°	3831
65°	2101
70°	888
75°	970
80°	673
85°	603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26298 cd/sqm



TEST NUMBER: P745621

CATALOG NUMBER: LD4D25D010-EU4DR6520359035-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.0	8.6
10°-20°	506.5	23.5
20°-30°	619.1	28.7
30°-40°	502.4	23.3
40°-50°	250.3	11.6
50°-60°	69.8	3.2
60°-70°	15.8	0.7
70°-80°	4.1	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1310.6	60.8
0°-40°	1813.0	84.2
0°-60°	2133.1	99.0
0°-90°	2154.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2154.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1956	
5°	1944	185
15°	1825	507
25°	1358	619
35°	809	502
45°	318	250
55°	72	70
65°	15	16
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P745621

CATALOG NUMBER: LD4D25D010-EU4DR6520359035-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1955.9
2.5°	1954.5
5°	1943.6
7.5°	1937.3
10°	1919.7
12.5°	1884.1
15°	1824.9
17.5°	1732.3
20°	1616.2
22.5°	1490.9
25°	1358.4
27.5°	1216.7
30°	1079.6
32.5°	944.2
35°	809.1
37.5°	674.3
40°	546.1
42.5°	426.0
45°	318.4
47.5°	221.9
50°	150.9
52.5°	104.0
55°	71.6
57.5°	48.3
60°	32.8
62.5°	22.7
65°	15.2
67.5°	7.7
70°	5.2
72.5°	4.9
75°	4.3
77.5°	2.9
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)