

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747209

Luminaire Tested: LD4D35BD010-EU4DR5520359050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR5520359050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3847.6 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P747209
CATALOG NUMBER: LD4D35BD010-EU4DR5520359050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P747209

CATALOG NUMBER: LD4D35BD010-EU4DR5520359050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 95 | 98 | 95 | 92 | 95 | 93 | 90 | 92 | 90 | 89 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 95 | 90 | 86 | 92 | 88 | 85 | 90 | 86 | 84 | 87 | 85 | 82 | 81 | | | | | | | | | | | | | | | | | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 82 | 79 | 77 | 75 | | | | | | | | | | | | | | | | | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 77 | 73 | 81 | 76 | 73 | 79 | 75 | 72 | 78 | 74 | 71 | 70 | | | | | | | | | | | | | | | | | | | |
| 6 | 88 | 79 | 73 | 68 | 86 | 78 | 72 | 68 | 76 | 71 | 68 | 75 | 70 | 67 | 74 | 70 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 7 | 83 | 74 | 68 | 64 | 82 | 73 | 67 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 65 | 62 | 61 | | | | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 9 | 75 | 66 | 60 | 56 | 74 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 54 | | | | | | | | | | | | | | | | | | | |
| 10 | 72 | 62 | 56 | 52 | 71 | 61 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 59 | 55 | 52 | 50 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 471416 |
| 5° | 452696 |
| 10° | 450986 |
| 15° | 438027 |
| 20° | 392758 |
| 25° | 324597 |
| 30° | 245186 |
| 35° | 177786 |
| 40° | 113776 |
| 45° | 51964 |
| 50° | 16998 |
| 55° | 7334 |
| 60° | 3147 |
| 65° | 414 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 51964 cd/sqm



TEST NUMBER: P747209

CATALOG NUMBER: LD4D35BD010-EU4DR5520359050-4LBS1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 392.7 | 10.2 |
| 10°-20° | 1071.9 | 27.9 |
| 20°-30° | 1221.5 | 31.7 |
| 30°-40° | 831.6 | 21.6 |
| 40°-50° | 286.5 | 7.4 |
| 50°-60° | 39.6 | 1.0 |
| 60°-70° | 3.8 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2686.1 | 69.8 |
| 0°-40° | 3517.7 | 91.4 |
| 0°-60° | 3843.8 | 99.9 |
| 0°-90° | 3847.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3847.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4315 | |
| 5° | 4128 | 393 |
| 15° | 3872 | 1072 |
| 25° | 2692 | 1222 |
| 35° | 1333 | 832 |
| 45° | 336 | 287 |
| 55° | 38 | 40 |
| 65° | 2 | 4 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P747209

CATALOG NUMBER: LD4D35BD010-EU4DR5520359050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4314.6 |
| 2.5° | 4215.7 |
| 5° | 4127.5 |
| 7.5° | 4084.1 |
| 10° | 4064.9 |
| 12.5° | 4000.7 |
| 15° | 3872.4 |
| 17.5° | 3668.7 |
| 20° | 3377.9 |
| 22.5° | 3042.1 |
| 25° | 2692.5 |
| 27.5° | 2328.4 |
| 30° | 1943.4 |
| 32.5° | 1617.3 |
| 35° | 1332.9 |
| 37.5° | 1062.3 |
| 40° | 797.7 |
| 42.5° | 552.8 |
| 45° | 336.3 |
| 47.5° | 181.2 |
| 50° | 100.0 |
| 52.5° | 59.3 |
| 55° | 38.5 |
| 57.5° | 24.6 |
| 60° | 14.4 |
| 62.5° | 6.4 |
| 65° | 1.6 |
| 67.5° | 0.5 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)