

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745699

Luminaire Tested: LD4D25D010-EU4DR7020359035-4LBS1B

Issue Date: 1/31/2024

Test Information

Test Method: LM-79-2019
Report Number: P745699
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/31/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR7020359035-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2487.8 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745699
CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P745699

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78															
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71				71															
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65															
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60				60															
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56				56															
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51				51															
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48				48															
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44				44															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214544
5°	214015
10°	213549
15°	213493
20°	211396
25°	198580
30°	177045
35°	141159
40°	93722
45°	56028
50°	29050
55°	15277
60°	5397
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56028 cd/sqm



TEST NUMBER: P745699

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.6	7.5
10°-20°	532.2	21.4
20°-30°	750.8	30.2
30°-40°	648.1	26.1
40°-50°	290.2	11.7
50°-60°	76.0	3.1
60°-70°	4.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1468.5	59.0
0°-40°	2116.7	85.1
0°-60°	2482.9	99.8
0°-90°	2487.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2487.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1964	
5°	1951	186
15°	1887	532
25°	1647	751
35°	1058	648
45°	363	290
55°	80	76
65°	0	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745699

CATALOG NUMBER: LD4D25D010-EU4DR7020359035-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1963.6
2.5°	1961.5
5°	1951.3
7.5°	1942.8
10°	1924.8
12.5°	1908.6
15°	1887.4
17.5°	1863.0
20°	1818.1
22.5°	1744.3
25°	1647.2
27.5°	1534.6
30°	1403.3
32.5°	1242.6
35°	1058.3
37.5°	854.9
40°	657.1
42.5°	499.3
45°	362.6
47.5°	250.0
50°	170.9
52.5°	117.9
55°	80.2
57.5°	48.4
60°	24.7
62.5°	7.8
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)