

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748003

Luminaire Tested: LD4D40BD010-EU4DR6040509024-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P748003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6040509024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3233.9 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748003
CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748003

CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70				
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65				
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57				
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	353601
5°	352736
10°	364447
15°	364830
20°	335680
25°	285513
30°	217556
35°	153844
40°	90342
45°	36451
50°	12171
55°	5867
60°	2404
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36451 cd/sqm



TEST NUMBER: P748003

CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.2	9.6
10°-20°	893.5	27.6
20°-30°	1069.4	33.1
30°-40°	715.3	22.1
40°-50°	212.1	6.6
50°-60°	30.5	0.9
60°-70°	2.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2273.2	70.3
0°-40°	2988.4	92.4
0°-60°	3231.0	99.9
0°-90°	3233.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3233.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3236	
5°	3216	310
15°	3225	894
25°	2368	1069
35°	1153	715
45°	236	212
55°	31	30
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P748003

CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3236.3
2.5°	3232.1
5°	3216.1
7.5°	3259.7
10°	3284.9
12.5°	3280.3
15°	3225.3
17.5°	3095.4
20°	2887.0
22.5°	2636.9
25°	2368.3
27.5°	2065.9
30°	1724.4
32.5°	1419.6
35°	1153.4
37.5°	886.8
40°	633.4
42.5°	417.7
45°	235.9
47.5°	120.7
50°	71.6
52.5°	46.4
55°	30.8
57.5°	19.7
60°	11.0
62.5°	4.6
65°	1.4
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)