

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745553

Luminaire Tested: LD4D25D010-EU4DR6020359040-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745553  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR6020359040-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2592.4 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745553  
CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P745553

CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	336392
5°	344663
10°	348826
15°	332298
20°	292984
25°	236977
30°	160291
35°	80323
40°	13022
45°	12763
50°	13003
55°	13201
60°	13570
65°	13883
70°	14216
75°	14353
80°	13905
85°	11533

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 14353 cd/sqm



TEST NUMBER: P745553

CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	300.3	11.6
10°-20°	812.6	31.3
20°-30°	874.3	33.7
30°-40°	380.0	14.7
40°-50°	63.9	2.5
50°-60°	62.0	2.4
60°-70°	53.1	2.0
70°-80°	35.5	1.4
80°-90°	10.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1987.2	76.7
0°-40°	2367.2	91.3
0°-60°	2493.1	96.2
0°-90°	2592.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2592.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3079	
5°	3142	300
15°	2938	813
25°	1966	874
35°	602	380
45°	83	64
55°	69	62
65°	54	53
75°	34	36
85°	9	11
90°	0	



TEST NUMBER: P745553

CATALOG NUMBER: LD4D25D010-EU4DR6020359040-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3078.8
2.5°	3165.3
5°	3142.5
7.5°	3149.7
10°	3144.1
12.5°	3079.2
15°	2937.7
17.5°	2747.8
20°	2519.8
22.5°	2275.8
25°	1965.7
27.5°	1572.2
30°	1270.5
32.5°	979.2
35°	602.2
37.5°	257.7
40°	91.3
42.5°	84.2
45°	82.6
47.5°	79.8
50°	76.5
52.5°	72.9
55°	69.3
57.5°	65.7
60°	62.1
62.5°	58.1
65°	53.7
67.5°	49.3
70°	44.5
72.5°	39.2
75°	34.0
77.5°	28.1
80°	22.1
82.5°	15.6
85°	9.2
87.5°	3.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)