

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745636

Luminaire Tested: LD4D25D010-EU4DR6520359040-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6520359040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2503.5 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745636
CATALOG NUMBER: LD4D25D010-EU4DR6520359040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P745636

CATALOG NUMBER: LD4D25D010-EU4DR6520359040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132764
5°	132427
10°	132315
15°	128232
20°	116740
25°	101734
30°	84609
35°	67041
40°	48390
45°	30569
50°	15937
55°	8472
60°	4450
65°	2446
70°	1025
75°	1128
80°	774
85°	670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30569 cd/sqm



TEST NUMBER: P745636

CATALOG NUMBER: LD4D25D010-EU4DR6520359040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.0	8.6
10°-20°	588.7	23.5
20°-30°	719.5	28.7
30°-40°	583.8	23.3
40°-50°	290.9	11.6
50°-60°	81.1	3.2
60°-70°	18.4	0.7
70°-80°	4.8	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1523.2	60.8
0°-40°	2107.0	84.2
0°-60°	2479.1	99.0
0°-90°	2503.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2503.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2273	
5°	2259	215
15°	2121	589
25°	1579	720
35°	940	584
45°	370	291
55°	83	81
65°	18	18
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P745636

CATALOG NUMBER: LD4D25D010-EU4DR6520359040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2273.2
2.5°	2271.5
5°	2258.8
7.5°	2251.5
10°	2231.1
12.5°	2189.6
15°	2120.8
17.5°	2013.3
20°	1878.3
22.5°	1732.7
25°	1578.7
27.5°	1414.0
30°	1254.6
32.5°	1097.3
35°	940.3
37.5°	783.7
40°	634.7
42.5°	495.0
45°	370.1
47.5°	257.9
50°	175.4
52.5°	120.9
55°	83.2
57.5°	56.1
60°	38.1
62.5°	26.4
65°	17.7
67.5°	9.0
70°	6.0
72.5°	5.7
75°	5.0
77.5°	3.3
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)