

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744941

Luminaire Tested: LD4D25D010-EU4DR2015309050-4LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744941  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR2015309050-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2320.5 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744941  
CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P744941

CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	100	99	98	98	96	95	97													
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	98	96	95	98	96	95	94													
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	98	96	95	98	96	95	94													
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	98	96	95	98	96	95	94													
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	98	96	95	98	96	95	94													
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	98	96	95	98	96	95	94													
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	98	96	95	98	96	95	94													
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	98	96	95	98	96	95	94													
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	98	96	95	98	96	95	94													
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	98	96	95	98	96	95	94													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1443061
5°	1301912
10°	730703
15°	371425
20°	157259
25°	72599
30°	38429
35°	20701
40°	11068
45°	6536
50°	3791
55°	2019
60°	1289
65°	905
70°	383
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6536 cd/sqm



TEST NUMBER: P744941

CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	940.4	40.5
10°-20°	925.9	39.9
20°-30°	302.5	13.0
30°-40°	103.0	4.4
40°-50°	34.6	1.5
50°-60°	10.4	0.4
60°-70°	3.5	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2168.8	93.5
0°-40°	2271.8	97.9
0°-60°	2316.8	99.8
0°-90°	2320.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2320.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13208	
5°	11870	940
15°	3284	926
25°	602	303
35°	155	103
45°	42	35
55°	11	10
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744941

CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13207.5
0.5°	13207.5
1°	13191.0
1.5°	13158.1
2°	13098.1
2.5°	13018.1
3°	12905.2
3.5°	12747.6
4°	12513.6
4.5°	12229.0
5°	11870.3
5.5°	11398.7
6°	10915.3
6.5°	10361.4
7°	9819.2
7.5°	9184.1
8°	8617.2
8.5°	8046.8
9°	7519.9
9.5°	7036.6
10°	6586.1
12.5°	4729.1
15°	3283.6
17.5°	2145.2
20°	1352.5
22.5°	876.2
25°	602.2
27.5°	423.4
30°	304.6
32.5°	218.8
35°	155.2
37.5°	108.2
40°	77.6
42.5°	56.5
45°	42.3
47.5°	32.9
50°	22.3
52.5°	14.1
55°	10.6
57.5°	8.2
60°	5.9
62.5°	4.7
65°	3.5



TEST NUMBER: P744941  
CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBDP1B

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.4
70°		1.2

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)