

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744945

Luminaire Tested: LD4D25D010-EU4DR2015309050-4LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR2015309050-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2666.5 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744945  
CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P744945

CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76	75															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1658218
5°	1496020
10°	839653
15°	426806
20°	180711
25°	83413
30°	44157
35°	23795
40°	12723
45°	7525
50°	4368
55°	2324
60°	1486
65°	1060
70°	447
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7525 cd/sqm



TEST NUMBER: P744945

CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1080.6	40.5
10°-20°	1064.0	39.9
20°-30°	347.6	13.0
30°-40°	118.3	4.4
40°-50°	39.8	1.5
50°-60°	12.0	0.5
60°-70°	4.0	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2492.1	93.5
0°-40°	2610.5	97.9
0°-60°	2662.3	99.8
0°-90°	2666.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2666.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15177	
5°	13640	###
15°	3773	1064
25°	692	348
35°	178	118
45°	49	40
55°	12	12
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744945  
CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15176.7
0.5°	15176.7
1°	15157.8
1.5°	15119.9
2°	15051.0
2.5°	14959.1
3°	14829.4
3.5°	14648.3
4°	14379.4
4.5°	14052.3
5°	13640.1
5.5°	13098.2
6°	12542.7
6.5°	11906.2
7°	11283.2
7.5°	10553.4
8°	9902.0
8.5°	9246.6
9°	8641.1
9.5°	8085.7
10°	7568.1
12.5°	5434.2
15°	3773.2
17.5°	2465.0
20°	1554.2
22.5°	1006.8
25°	691.9
27.5°	486.5
30°	350.0
32.5°	251.4
35°	178.4
37.5°	124.3
40°	89.2
42.5°	64.9
45°	48.7
47.5°	37.8
50°	25.7
52.5°	16.2
55°	12.2
57.5°	9.5
60°	6.8
62.5°	5.4
65°	4.1



TEST NUMBER: P744945  
CATALOG NUMBER: LD4D25D010-EU4DR2015309050-4LBS1B

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.7
70°		1.4

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)