

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745969

Luminaire Tested: LD4D30D010-EU4DR3020359024-4LBDP1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745969  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR3020359024-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2281.7 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745969  
CATALOG NUMBER: LD4D30D010-EU4DR3020359024-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P745969

CATALOG NUMBER: LD4D30D010-EU4DR3020359024-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	561576	561576	561576
5°	545457	544819	545488
10°	472447	469120	472338
15°	308250	306593	305048
20°	153275	159026	153072
25°	77210	87066	75631
30°	30917	33683	26940
35°	14334	13736	11512
40°	6185	6875	5825
45°	4362	5423	4406
50°	1500	3942	1584
55°	867	1641	907
60°	612	720	612
65°	398	398	398
70°	246	157	246
75°	0	89	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 5423 cd/sqm



TEST NUMBER: P745969

CATALOG NUMBER: LD4D30D010-EU4DR3020359024-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	645.2	28.3
10°-20°	1039.0	45.5
20°-30°	449.0	19.7
30°-40°	102.3	4.5
40°-50°	35.1	1.5
50°-60°	8.6	0.4
60°-70°	2.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2133.2	93.5
0°-40°	2235.5	98.0
0°-60°	2279.2	99.9
0°-90°	2281.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2281.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	7337	7337	7337	7337	7337	
5°	7099	7092	7091	7106	7099	646
15°	3890	3843	3869	3856	3850	1042
25°	914	949	1031	925	896	438
35°	153	157	147	146	123	104
45°	40	50	50	50	41	29
55°	6	7	12	7	7	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P745969

CATALOG NUMBER: LD4D30D010-EU4DR3020359024-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	7336.7	7336.7	7336.7	7336.7	7336.7
2.5°	7288.1	7283.1	7285.9	7289.5	7291.0
5°	7099.0	7092.2	7090.7	7105.5	7099.4
7.5°	6717.6	6707.8	6693.0	6726.6	6757.9
10°	6078.5	6067.7	6035.7	6051.5	6077.1
12.5°	5135.1	5100.2	5099.5	5149.9	5143.1
15°	3889.9	3843.1	3869.0	3856.4	3849.5
17.5°	2615.9	2597.8	2632.4	2621.9	2577.0
20°	1881.7	1886.4	1952.3	1919.2	1879.2
22.5°	1373.1	1390.0	1468.2	1382.8	1351.5
25°	914.2	948.8	1030.9	924.7	895.5
27.5°	562.3	578.2	661.4	555.1	539.3
30°	349.8	341.8	381.1	327.1	304.8
32.5°	229.5	219.4	232.0	208.2	190.2
35°	153.4	156.7	147.0	145.9	123.2
37.5°	95.8	110.2	97.2	103.8	79.2
40°	61.9	80.0	68.8	76.0	58.3
42.5°	50.8	61.6	56.6	60.2	51.9
45°	40.3	50.1	50.1	50.1	40.7
47.5°	22.3	33.5	42.9	34.2	23.8
50°	12.6	16.9	33.1	17.6	13.3
52.5°	8.7	9.7	22.7	10.1	9.0
55°	6.5	6.8	12.3	7.2	6.8
57.5°	5.0	5.4	6.5	5.4	5.0
60°	4.0	4.0	4.7	4.3	4.0
62.5°	2.9	2.9	3.3	2.9	2.9
65°	2.2	2.2	2.2	2.2	2.2
67.5°	1.1	1.4	1.4	1.4	1.4
70°	1.1	0.7	0.7	0.7	1.1
72.5°	0.7	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)