

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746219

Luminaire Tested: LD4D30D010-EU4DR4520359027-4LBS1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746219  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR4520359027-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2618.7 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746219  
CATALOG NUMBER: LD4D30D010-EU4DR4520359027-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P746219

CATALOG NUMBER: LD4D30D010-EU4DR4520359027-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20												
RC	80					70					50					30					10					0							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0						
RCR																																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								100							
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95								95							
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90								90							
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85								85							
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81								81							
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77								77							
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73								73							
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69								69							
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66								66							
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63								63							
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60								60							

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	505746
5°	491336
10°	470079
15°	430222
20°	341319
25°	213095
30°	117446
35°	52740
40°	20767
45°	9796
50°	4640
55°	2419
60°	1180
65°	284
70°	96
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9796 cd/sqm



TEST NUMBER: P746219

CATALOG NUMBER: LD4D30D010-EU4DR4520359027-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	420.9	16.1
10°-20°	1035.9	39.6
20°-30°	820.4	31.3
30°-40°	273.2	10.4
40°-50°	54.2	2.1
50°-60°	12.3	0.5
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2277.2	87.0
0°-40°	2550.4	97.4
0°-60°	2617.0	99.9
0°-90°	2618.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2618.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4629	
5°	4480	421
15°	3803	1036
25°	1768	820
35°	395	273
45°	63	54
55°	13	12
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746219

CATALOG NUMBER: LD4D30D010-EU4DR4520359027-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4628.8
2.5°	4598.6
5°	4479.8
7.5°	4381.9
10°	4237.0
12.5°	4044.1
15°	3803.4
17.5°	3441.5
20°	2935.5
22.5°	2332.6
25°	1767.6
27.5°	1294.2
30°	930.9
32.5°	633.1
35°	395.4
37.5°	234.5
40°	145.6
42.5°	95.7
45°	63.4
47.5°	40.8
50°	27.3
52.5°	18.2
55°	12.7
57.5°	8.4
60°	5.4
62.5°	2.9
65°	1.1
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)