

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748192

Luminaire Tested: LD4D40BD010-EU4DR7040509035-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748192  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR7040509035-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3837.3 lumens  
Efficiency: N/A  
Efficacy: 109.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P748192  
CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P748192  
 CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	471384
5°	457369
10°	444628
15°	438796
20°	409746
25°	307815
30°	217607
35°	77082
40°	40535
45°	43172
50°	44705
55°	45546
60°	45824
65°	44855
70°	42328
75°	39218
80°	34795
85°	28207

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 45835 cd/sqm



TEST NUMBER: P748192

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	393.3	10.3
10°-20°	1078.9	28.1
20°-30°	1188.3	31.0
30°-40°	454.0	11.8
40°-50°	214.4	5.6
50°-60°	213.1	5.6
60°-70°	170.6	4.4
70°-80°	98.1	2.6
80°-90°	26.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2660.5	69.3
0°-40°	3114.5	81.2
0°-60°	3542.0	92.3
0°-90°	3837.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3837.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4314	
5°	4170	393
15°	3879	1079
25°	2553	1188
35°	578	454
45°	279	214
55°	239	213
65°	174	171
75°	93	98
85°	22	27
90°	0	



TEST NUMBER: P748192

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4314.3
2.5°	4269.2
5°	4170.1
7.5°	4087.5
10°	4007.6
12.5°	3940.0
15°	3879.2
17.5°	3732.3
20°	3524.0
22.5°	3074.5
25°	2553.3
27.5°	2222.7
30°	1724.8
32.5°	1114.1
35°	577.9
37.5°	312.2
40°	284.2
42.5°	282.1
45°	279.4
47.5°	273.2
50°	263.0
52.5°	251.4
55°	239.1
57.5°	225.4
60°	209.7
62.5°	191.9
65°	173.5
67.5°	153.0
70°	132.5
72.5°	112.0
75°	92.9
77.5°	73.1
80°	55.3
82.5°	38.9
85°	22.5
87.5°	8.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)