

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747828

Luminaire Tested: LD4D40BD010-EU4DR4540509050-4LBDP1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747828  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR4540509050-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4104.8 lumens  
Efficiency: N/A  
Efficacy: 116.6 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P747828

CATALOG NUMBER: LD4D40BD010-EU4DR4540509050-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P747828

CATALOG NUMBER: LD4D40BD010-EU4DR4540509050-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95	95	95		
	2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90	90	90	90	90		
	3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85	85	85		
	4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81	81	81		
	5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77	77	77	77	77		
	6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73	73	73		
	7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	69	69	69	69		
	8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66	66	66		
	9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63	63	63	63	63		
	10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60	60	60	60	60	60		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	792709
5°	770138
10°	736816
15°	674335
20°	534983
25°	334000
30°	184085
35°	82657
40°	32562
45°	15344
50°	7275
55°	3810
60°	1879
65°	440
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15344 cd/sqm



TEST NUMBER: P747828

CATALOG NUMBER: LD4D40BD010-EU4DR4540509050-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	659.8	16.1
10°-20°	1623.8	39.6
20°-30°	1285.9	31.3
30°-40°	428.2	10.4
40°-50°	85.0	2.1
50°-60°	19.3	0.5
60°-70°	2.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3569.4	87.0
0°-40°	3997.6	97.4
0°-60°	4101.9	99.9
0°-90°	4104.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4104.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7255	
5°	7022	660
15°	5962	1624
25°	2770	1286
35°	620	428
45°	99	85
55°	20	19
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747828

CATALOG NUMBER: LD4D40BD010-EU4DR4540509050-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7255.2
2.5°	7207.8
5°	7021.8
7.5°	6868.3
10°	6641.2
12.5°	6338.7
15°	5961.5
17.5°	5394.3
20°	4601.1
22.5°	3656.1
25°	2770.5
27.5°	2028.7
30°	1459.1
32.5°	992.4
35°	619.7
37.5°	367.5
40°	228.3
42.5°	150.1
45°	99.3
47.5°	63.9
50°	42.8
52.5°	28.5
55°	20.0
57.5°	13.1
60°	8.6
62.5°	4.6
65°	1.7
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)