

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746634

Luminaire Tested: LD4D30D010-EU4DR7020359035-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P746634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR7020359035-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2229.2 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746634

CATALOG NUMBER: LD4D30D010-EU4DR7020359035-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P746634

CATALOG NUMBER: LD4D30D010-EU4DR7020359035-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	273829
5°	265695
10°	258294
15°	254905
20°	238022
25°	178821
30°	126403
35°	44777
40°	23548
45°	25078
50°	25956
55°	26459
60°	26616
65°	26060
70°	24598
75°	22796
80°	20198
85°	16423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 26619 cd/sqm



TEST NUMBER: P746634

CATALOG NUMBER: LD4D30D010-EU4DR7020359035-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.5	10.3
10°-20°	626.8	28.1
20°-30°	690.3	31.0
30°-40°	263.7	11.8
40°-50°	124.5	5.6
50°-60°	123.8	5.6
60°-70°	99.1	4.4
70°-80°	57.0	2.6
80°-90°	15.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1545.5	69.3
0°-40°	1809.3	81.2
0°-60°	2057.6	92.3
0°-90°	2229.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2229.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2506	
5°	2422	228
15°	2254	627
25°	1483	690
35°	336	264
45°	162	125
55°	139	124
65°	101	99
75°	54	57
85°	13	15
90°	0	



TEST NUMBER: P746634

CATALOG NUMBER: LD4D30D010-EU4DR7020359035-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2506.2
2.5°	2480.0
5°	2422.5
7.5°	2374.5
10°	2328.1
12.5°	2288.8
15°	2253.5
17.5°	2168.2
20°	2047.1
22.5°	1786.0
25°	1483.3
27.5°	1291.2
30°	1001.9
32.5°	647.2
35°	335.7
37.5°	181.3
40°	165.1
42.5°	163.9
45°	162.3
47.5°	158.7
50°	152.7
52.5°	146.0
55°	138.9
57.5°	130.9
60°	121.8
62.5°	111.5
65°	100.8
67.5°	88.9
70°	77.0
72.5°	65.1
75°	54.0
77.5°	42.5
80°	32.1
82.5°	22.6
85°	13.1
87.5°	5.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)