

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745869

Luminaire Tested: LD4D30D010-EU4DR2015309040-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR2015309040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3240.8 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745869
CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P745869

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97	97	97													
	2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94	94	94													
	3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91	91	91													
	4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88	88	88													
	5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85	85	85													
	6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83	83	83													
	7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81	81	81													
	8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79	79	79													
	9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77	77	77													
	10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75	75	75													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2015457
5°	1818321
10°	1020539
15°	518757
20°	219639
25°	101388
30°	53670
35°	28917
40°	15461
45°	9132
50°	5303
55°	2819
60°	1792
65°	1267
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9132 cd/sqm



TEST NUMBER: P745869

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1313.3	40.5
10°-20°	1293.2	39.9
20°-30°	422.5	13.0
30°-40°	143.8	4.4
40°-50°	48.4	1.5
50°-60°	14.6	0.4
60°-70°	4.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3029.0	93.5
0°-40°	3172.9	97.9
0°-60°	3235.8	99.8
0°-90°	3240.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3240.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18446	
5°	16579	###
15°	4586	1293
25°	841	422
35°	217	144
45°	59	48
55°	15	15
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745869

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	18446.3
0.5°	18446.3
1°	18423.4
1.5°	18377.4
2°	18293.6
2.5°	18181.9
3°	18024.2
3.5°	17804.1
4°	17477.2
4.5°	17079.7
5°	16578.7
5.5°	15920.0
6°	15244.9
6.5°	14471.3
7°	13714.0
7.5°	12827.0
8°	12035.3
8.5°	11238.6
9°	10502.8
9.5°	9827.6
10°	9198.5
12.5°	6604.9
15°	4586.1
17.5°	2996.1
20°	1889.0
22.5°	1223.7
25°	841.0
27.5°	591.3
30°	425.4
32.5°	305.5
35°	216.8
37.5°	151.1
40°	108.4
42.5°	78.8
45°	59.1
47.5°	46.0
50°	31.2
52.5°	19.7
55°	14.8
57.5°	11.5
60°	8.2
62.5°	6.6
65°	4.9



TEST NUMBER: P745869
CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.3
70°		1.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)