

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748139

Luminaire Tested: LD4D40BD010-EU4DR6540509050-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6540509050-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2615.9 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748139
CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P748139

CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	281401
5°	281631
10°	291545
15°	292029
20°	268869
25°	229080
30°	175380
35°	123899
40°	73141
45°	29683
50°	10760
55°	6000
60°	3431
65°	1887
70°	1981
75°	1562
80°	1636
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29683 cd/sqm



TEST NUMBER: P748139

CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.0	9.5
10°-20°	715.4	27.3
20°-30°	858.3	32.8
30°-40°	576.8	22.1
40°-50°	172.7	6.6
50°-60°	30.5	1.2
60°-70°	8.6	0.3
70°-80°	4.3	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1821.7	69.6
0°-40°	2398.5	91.7
0°-60°	2601.6	99.5
0°-90°	2615.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2615.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2576	
5°	2568	248
15°	2582	715
25°	1900	858
35°	929	577
45°	192	173
55°	32	30
65°	7	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P748139

CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2575.5
2.5°	2586.5
5°	2567.8
7.5°	2606.6
10°	2627.8
12.5°	2622.7
15°	2581.7
17.5°	2481.4
20°	2312.4
22.5°	2113.3
25°	1900.2
27.5°	1659.8
30°	1390.1
32.5°	1145.6
35°	928.9
37.5°	714.8
40°	512.8
42.5°	334.9
45°	192.1
47.5°	101.7
50°	63.3
52.5°	43.9
55°	31.5
57.5°	22.7
60°	15.7
62.5°	10.2
65°	7.3
67.5°	6.6
70°	6.2
72.5°	4.8
75°	3.7
77.5°	3.3
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)