

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748935

Luminaire Tested: LD4D45BD010-EU4DR7040509024-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR7040509024-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2784.0 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748935
CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748935
 CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	341997
5°	331831
10°	322587
15°	318351
20°	297275
25°	223330
30°	157868
35°	55927
40°	29410
45°	31321
50°	32432
55°	33050
60°	33237
65°	32549
70°	30700
75°	28453
80°	25231
85°	20559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 33248 cd/sqm



TEST NUMBER: P748935

CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	285.4	10.3
10°-20°	782.8	28.1
20°-30°	862.1	31.0
30°-40°	329.4	11.8
40°-50°	155.5	5.6
50°-60°	154.6	5.6
60°-70°	123.8	4.4
70°-80°	71.1	2.6
80°-90°	19.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1930.2	69.3
0°-40°	2259.6	81.2
0°-60°	2569.8	92.3
0°-90°	2784.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2784.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3130	
5°	3026	285
15°	2814	783
25°	1852	862
35°	419	329
45°	203	156
55°	174	155
65°	126	124
75°	67	71
85°	16	19
90°	0	



TEST NUMBER: P748935

CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3130.1
2.5°	3097.4
5°	3025.5
7.5°	2965.5
10°	2907.6
12.5°	2858.5
15°	2814.4
17.5°	2707.8
20°	2556.7
22.5°	2230.6
25°	1852.5
27.5°	1612.6
30°	1251.3
32.5°	808.3
35°	419.3
37.5°	226.5
40°	206.2
42.5°	204.7
45°	202.7
47.5°	198.2
50°	190.8
52.5°	182.4
55°	173.5
57.5°	163.5
60°	152.1
62.5°	139.3
65°	125.9
67.5°	111.0
70°	96.1
72.5°	81.3
75°	67.4
77.5°	53.0
80°	40.1
82.5°	28.2
85°	16.4
87.5°	6.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)