

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746501

Luminaire Tested: LD4D30D010-EU4DR6020359050-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746501  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR6020359050-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2267.4 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746501  
CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P746501

CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	294217
5°	301461
10°	305091
15°	290649
20°	256265
25°	207272
30°	140193
35°	70253
40°	11396
45°	11156
50°	11372
55°	11544
60°	11866
65°	12151
70°	12427
75°	12580
80°	12144
85°	10154

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 12580 cd/sqm



TEST NUMBER: P746501

CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	262.7	11.6
10°-20°	710.7	31.3
20°-30°	764.7	33.7
30°-40°	332.4	14.7
40°-50°	55.8	2.5
50°-60°	54.3	2.4
60°-70°	46.4	2.0
70°-80°	31.1	1.4
80°-90°	9.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1738.1	76.7
0°-40°	2070.5	91.3
0°-60°	2180.6	96.2
0°-90°	2267.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2267.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2693	
5°	2749	263
15°	2570	711
25°	1719	765
35°	527	332
45°	72	56
55°	61	54
65°	47	46
75°	30	31
85°	8	9
90°	0	



TEST NUMBER: P746501  
CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2692.8
2.5°	2768.6
5°	2748.6
7.5°	2754.9
10°	2749.9
12.5°	2693.2
15°	2569.5
17.5°	2403.4
20°	2204.0
22.5°	1990.5
25°	1719.3
27.5°	1375.1
30°	1111.2
32.5°	856.5
35°	526.7
37.5°	225.3
40°	79.9
42.5°	73.6
45°	72.2
47.5°	69.7
50°	66.9
52.5°	63.8
55°	60.6
57.5°	57.5
60°	54.3
62.5°	50.8
65°	47.0
67.5°	43.1
70°	38.9
72.5°	34.3
75°	29.8
77.5°	24.5
80°	19.3
82.5°	13.7
85°	8.1
87.5°	2.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)