

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746503

Luminaire Tested: LD4D30D010-EU4DR6020359050-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746503  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR6020359050-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3023.3 lumens  
Efficiency: N/A  
Efficacy: 104.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746503  
CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P746503

CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	392312
5°	401959
10°	406807
15°	387543
20°	341691
25°	276362
30°	186936
35°	93675
40°	15190
45°	14880
50°	15179
55°	15392
60°	15821
65°	16184
70°	16580
75°	16759
80°	16171
85°	13539

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 16759 cd/sqm



TEST NUMBER: P746503

CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	350.3	11.6
10°-20°	947.7	31.3
20°-30°	1019.6	33.7
30°-40°	443.2	14.7
40°-50°	74.4	2.5
50°-60°	72.4	2.4
60°-70°	61.9	2.0
70°-80°	41.4	1.4
80°-90°	12.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2317.5	76.7
0°-40°	2760.7	91.3
0°-60°	2907.6	96.2
0°-90°	3023.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3023.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3591	
5°	3665	350
15°	3426	948
25°	2292	1020
35°	702	443
45°	96	74
55°	81	72
65°	63	62
75°	40	41
85°	11	12
90°	0	



TEST NUMBER: P746503

CATALOG NUMBER: LD4D30D010-EU4DR6020359050-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3590.6
2.5°	3691.5
5°	3664.9
7.5°	3673.2
10°	3666.7
12.5°	3591.0
15°	3426.1
17.5°	3204.6
20°	2938.7
22.5°	2654.1
25°	2292.4
27.5°	1833.6
30°	1481.7
32.5°	1142.0
35°	702.3
37.5°	300.5
40°	106.5
42.5°	98.1
45°	96.3
47.5°	93.0
50°	89.3
52.5°	85.0
55°	80.8
57.5°	76.7
60°	72.4
62.5°	67.8
65°	62.6
67.5°	57.5
70°	51.9
72.5°	45.8
75°	39.7
77.5°	32.7
80°	25.7
82.5°	18.2
85°	10.8
87.5°	3.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)