

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748792

Luminaire Tested: LD4D45BD010-EU4DR6040509027-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6040509027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3632.6 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748792

CATALOG NUMBER: LD4D45BD010-EU4DR6040509027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748792

CATALOG NUMBER: LD4D45BD010-EU4DR6040509027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	471373
5°	482968
10°	488796
15°	465649
20°	410559
25°	332071
30°	224621
35°	112562
40°	18257
45°	17878
50°	18222
55°	18497
60°	19011
65°	19442
70°	19902
75°	20137
80°	19443
85°	16172

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 20137 cd/sqm



TEST NUMBER: P748792

CATALOG NUMBER: LD4D45BD010-EU4DR6040509027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.9	11.6
10°-20°	1138.7	31.3
20°-30°	1225.1	33.7
30°-40°	532.5	14.7
40°-50°	89.4	2.5
50°-60°	87.0	2.4
60°-70°	74.4	2.0
70°-80°	49.8	1.4
80°-90°	14.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2784.6	76.7
0°-40°	3317.2	91.3
0°-60°	3493.6	96.2
0°-90°	3632.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3632.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4314	
5°	4404	421
15°	4117	1139
25°	2754	1225
35°	844	533
45°	116	89
55°	97	87
65°	75	74
75°	48	50
85°	13	15
90°	0	



TEST NUMBER: P748792

CATALOG NUMBER: LD4D45BD010-EU4DR6040509027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4314.2
2.5°	4435.5
5°	4403.5
7.5°	4413.6
10°	4405.7
12.5°	4314.8
15°	4116.6
17.5°	3850.4
20°	3531.0
22.5°	3189.1
25°	2754.5
27.5°	2203.1
30°	1780.4
32.5°	1372.2
35°	843.9
37.5°	361.0
40°	128.0
42.5°	117.9
45°	115.7
47.5°	111.7
50°	107.2
52.5°	102.2
55°	97.1
57.5°	92.1
60°	87.0
62.5°	81.4
65°	75.2
67.5°	69.1
70°	62.3
72.5°	55.0
75°	47.7
77.5°	39.3
80°	30.9
82.5°	21.9
85°	12.9
87.5°	4.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)