

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748874

Luminaire Tested: LD4D45BD010-EU4DR6540509027-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3505.7 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748874

CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748874

CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	185905
5°	185437
10°	185280
15°	179566
20°	163472
25°	142454
30°	118484
35°	93878
40°	67755
45°	42809
50°	22315
55°	11863
60°	6226
65°	3427
70°	1434
75°	1580
80°	1110
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42809 cd/sqm



TEST NUMBER: P748874

CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.0	8.6
10°-20°	824.3	23.5
20°-30°	1007.6	28.7
30°-40°	817.5	23.3
40°-50°	407.4	11.6
50°-60°	113.6	3.2
60°-70°	25.8	0.7
70°-80°	6.7	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2132.9	60.8
0°-40°	2950.4	84.2
0°-60°	3471.5	99.0
0°-90°	3505.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3505.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3183	
5°	3163	301
15°	2970	824
25°	2211	1008
35°	1317	818
45°	518	407
55°	116	114
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P748874

CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3183.1
2.5°	3180.8
5°	3163.0
7.5°	3152.7
10°	3124.2
12.5°	3066.2
15°	2969.8
17.5°	2819.2
20°	2630.2
22.5°	2426.3
25°	2210.6
27.5°	1980.0
30°	1756.9
32.5°	1536.6
35°	1316.7
37.5°	1097.4
40°	888.7
42.5°	693.2
45°	518.3
47.5°	361.1
50°	245.6
52.5°	169.3
55°	116.5
57.5°	78.6
60°	53.3
62.5°	37.0
65°	24.8
67.5°	12.6
70°	8.4
72.5°	8.0
75°	7.0
77.5°	4.7
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)