

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748958

Luminaire Tested: LD4D45BD010-EU4DR7040509030-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748958  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR7040509030-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2420.2 lumens  
Efficiency: N/A  
Efficacy: 62.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P748958  
CATALOG NUMBER: LD4D45BD010-EU4DR7040509030-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P748958

CATALOG NUMBER: LD4D45BD010-EU4DR7040509030-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	297288
5°	288453
10°	280417
15°	276736
20°	258416
25°	194131
30°	137241
35°	48618
40°	25559
45°	27226
50°	28200
55°	28726
60°	28910
65°	28284
70°	26707
75°	24738
80°	21959
85°	17801

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 28917 cd/sqm



TEST NUMBER: P748958

CATALOG NUMBER: LD4D45BD010-EU4DR7040509030-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	248.1	10.2
10°-20°	680.4	28.1
20°-30°	749.4	31.0
30°-40°	286.3	11.8
40°-50°	135.2	5.6
50°-60°	134.4	5.6
60°-70°	107.6	4.4
70°-80°	61.9	2.6
80°-90°	16.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1677.9	69.3
0°-40°	1964.2	81.2
0°-60°	2233.9	92.3
0°-90°	2420.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2420.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2721	
5°	2630	248
15°	2446	680
25°	1610	749
35°	364	286
45°	176	135
55°	151	134
65°	109	108
75°	59	62
85°	14	17
90°	0	



TEST NUMBER: P748958  
CATALOG NUMBER: LD4D45BD010-EU4DR7040509030-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2720.9
2.5°	2692.5
5°	2630.0
7.5°	2577.9
10°	2527.5
12.5°	2484.8
15°	2446.5
17.5°	2353.9
20°	2222.5
22.5°	1939.0
25°	1610.3
27.5°	1401.8
30°	1087.8
32.5°	702.6
35°	364.5
37.5°	196.9
40°	179.2
42.5°	177.9
45°	176.2
47.5°	172.3
50°	165.9
52.5°	158.5
55°	150.8
57.5°	142.2
60°	132.3
62.5°	121.1
65°	109.4
67.5°	96.5
70°	83.6
72.5°	70.7
75°	58.6
77.5°	46.1
80°	34.9
82.5°	24.6
85°	14.2
87.5°	5.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)