

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747243

Luminaire Tested: LD4D35BD010-EU4DR6020359030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6020359030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3204.7 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P747243

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P747243

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	415846
5°	426067
10°	431215
15°	410789
20°	362190
25°	292951
30°	198152
35°	99303
40°	16103
45°	15761
50°	16080
55°	16325
60°	16782
65°	17167
70°	17570
75°	17773
80°	17114
85°	14291

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 17773 cd/sqm



TEST NUMBER: P747243

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.3	11.6
10°-20°	1004.5	31.3
20°-30°	1080.8	33.7
30°-40°	469.8	14.7
40°-50°	78.9	2.5
50°-60°	76.7	2.4
60°-70°	65.6	2.0
70°-80°	43.9	1.4
80°-90°	13.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2456.6	76.7
0°-40°	2926.4	91.3
0°-60°	3082.0	96.2
0°-90°	3204.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3204.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3806	
5°	3885	371
15°	3632	1005
25°	2430	1081
35°	744	470
45°	102	79
55°	86	77
65°	66	66
75°	42	44
85°	11	13
90°	0	



TEST NUMBER: P747243

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3806.0
2.5°	3913.0
5°	3884.7
7.5°	3893.7
10°	3886.7
12.5°	3806.5
15°	3631.6
17.5°	3396.9
20°	3115.0
22.5°	2813.4
25°	2430.0
27.5°	1943.6
30°	1570.6
32.5°	1210.5
35°	744.5
37.5°	318.5
40°	112.9
42.5°	104.0
45°	102.0
47.5°	98.6
50°	94.6
52.5°	90.1
55°	85.7
57.5°	81.2
60°	76.8
62.5°	71.8
65°	66.4
67.5°	60.9
70°	55.0
72.5°	48.5
75°	42.1
77.5°	34.7
80°	27.2
82.5°	19.3
85°	11.4
87.5°	4.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)