

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747400

Luminaire Tested: LD4D35BD010-EU4DR7020359030-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747400  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR7020359030-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3387.0 lumens  
Efficiency: N/A  
Efficacy: 110.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P747400

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P747400

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	416065
5°	403703
10°	392450
15°	387295
20°	361655
25°	271697
30°	192059
35°	68039
40°	35772
45°	38104
50°	39452
55°	40193
60°	40448
65°	39581
70°	37376
75°	34616
80°	30705
85°	24947

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 40467 cd/sqm



TEST NUMBER: P747400

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	347.2	10.3
10°-20°	952.3	28.1
20°-30°	1048.8	31.0
30°-40°	400.7	11.8
40°-50°	189.2	5.6
50°-60°	188.1	5.6
60°-70°	150.6	4.4
70°-80°	86.6	2.6
80°-90°	23.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2348.3	69.3
0°-40°	2749.0	81.2
0°-60°	3126.3	92.3
0°-90°	3387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3387.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3808	
5°	3681	347
15°	3424	952
25°	2254	1049
35°	510	401
45°	247	189
55°	211	188
65°	153	151
75°	82	87
85°	20	24
90°	0	



TEST NUMBER: P747400

CATALOG NUMBER: LD4D35BD010-EU4DR7020359030-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3808.0
2.5°	3768.2
5°	3680.8
7.5°	3607.8
10°	3537.3
12.5°	3477.6
15°	3423.9
17.5°	3294.3
20°	3110.4
22.5°	2713.7
25°	2253.7
27.5°	1961.9
30°	1522.3
32.5°	983.3
35°	510.1
37.5°	275.5
40°	250.8
42.5°	249.0
45°	246.6
47.5°	241.2
50°	232.1
52.5°	221.9
55°	211.0
57.5°	199.0
60°	185.1
62.5°	169.4
65°	153.1
67.5°	135.1
70°	117.0
72.5°	98.9
75°	82.0
77.5°	64.5
80°	48.8
82.5°	34.4
85°	19.9
87.5°	7.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)