

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746945

Luminaire Tested: LD4D35BD010-EU4DR4020359035-4LBDP1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR4020359035-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3539.7 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P746945  
CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P746945

CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																											
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																											
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																											
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																											
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																											
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																											
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																											
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																											
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69																											
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	900473
5°	896092
10°	846997
15°	720057
20°	490776
25°	204776
30°	64381
35°	29931
40°	16545
45°	7587
50°	3689
55°	2019
60°	1049
65°	362
70°	160
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7587 cd/sqm



TEST NUMBER: P746945

CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	762.9	21.6
10°-20°	1709.1	48.3
20°-30°	855.5	24.2
30°-40°	156.8	4.4
40°-50°	43.3	1.2
50°-60°	10.2	0.3
60°-70°	1.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3327.5	94.0
0°-40°	3484.3	98.4
0°-60°	3537.7	99.9
0°-90°	3539.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3539.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8242	
5°	8170	763
15°	6366	1709
25°	1699	856
35°	224	157
45°	49	43
55°	11	10
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746945

CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8241.5
2.5°	8229.4
5°	8170.2
7.5°	7981.5
10°	7634.3
12.5°	7093.2
15°	6365.7
17.5°	5419.7
20°	4220.9
22.5°	2877.6
25°	1698.6
27.5°	897.9
30°	510.3
32.5°	329.8
35°	224.4
37.5°	160.3
40°	116.0
42.5°	79.4
45°	49.1
47.5°	31.3
50°	21.7
52.5°	15.4
55°	10.6
57.5°	6.7
60°	4.8
62.5°	2.9
65°	1.4
67.5°	1.0
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)