

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739934

Luminaire Tested: LD4D05D010-EU4DR200210IC9027-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P739934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR200210IC9027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 686.4 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739934
CATALOG NUMBER: LD4D05D010-EU4DR200210IC9027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P739934

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	100	99	98	97	97	97	97													
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	98	96	95	94	94	94	94													
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	98	96	95	94	94	94	94													
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	98	96	95	94	94	94	94													
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	98	96	95	94	94	94	94													
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	98	96	95	94	94	94	94													
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	98	96	95	94	94	94	94													
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	98	96	95	94	94	94	94													
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	98	96	95	94	94	94	94													
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	98	96	95	94	94	94	94													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	426871
5°	385113
10°	216146
15°	109869
20°	46521
25°	21471
30°	11367
35°	6122
40°	3280
45°	1931
50°	1122
55°	591
60°	371
65°	259
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1931 cd/sqm



TEST NUMBER: P739934

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.2	40.5
10°-20°	273.9	39.9
20°-30°	89.5	13.0
30°-40°	30.5	4.4
40°-50°	10.2	1.5
50°-60°	3.1	0.4
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	641.5	93.5
0°-40°	672.0	97.9
0°-60°	685.3	99.8
0°-90°	686.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3907	
5°	3511	278
15°	971	274
25°	178	89
35°	46	30
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739934

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9027-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3906.9
0.5°	3906.9
1°	3902.0
1.5°	3892.3
2°	3874.5
2.5°	3850.9
3°	3817.5
3.5°	3770.9
4°	3701.6
4.5°	3617.4
5°	3511.3
5.5°	3371.8
6°	3228.8
6.5°	3065.0
7°	2904.6
7.5°	2716.7
8°	2549.0
8.5°	2380.3
9°	2224.5
9.5°	2081.5
10°	1948.2
12.5°	1398.9
15°	971.3
17.5°	634.6
20°	400.1
22.5°	259.2
25°	178.1
27.5°	125.2
30°	90.1
32.5°	64.7
35°	45.9
37.5°	32.0
40°	23.0
42.5°	16.7
45°	12.5
47.5°	9.7
50°	6.6
52.5°	4.2
55°	3.1
57.5°	2.4
60°	1.7
62.5°	1.4
65°	1.0



TEST NUMBER: P739934
CATALOG NUMBER: LD4D05D010-EU4DR200210IC9027-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.7
70°		0.3

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)