

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747270

Luminaire Tested: LD4D35BD010-EU4DR6020359040-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747270  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR6020359040-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3559.4 lumens  
Efficiency: N/A  
Efficacy: 115.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P747270  
CATALOG NUMBER: LD4D35BD010-EU4DR6020359040-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P747270

CATALOG NUMBER: LD4D35BD010-EU4DR6020359040-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	461867
5°	473228
10°	478944
15°	456250
20°	402281
25°	325368
30°	220092
35°	110281
40°	17886
45°	17507
50°	17865
55°	18135
60°	18640
65°	19054
70°	19519
75°	19757
80°	19065
85°	15921

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 19757 cd/sqm



TEST NUMBER: P747270

CATALOG NUMBER: LD4D35BD010-EU4DR6020359040-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	412.4	11.6
10°-20°	1115.7	31.3
20°-30°	1200.4	33.7
30°-40°	521.8	14.7
40°-50°	87.6	2.5
50°-60°	85.2	2.4
60°-70°	72.9	2.0
70°-80°	48.8	1.4
80°-90°	14.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2728.5	76.7
0°-40°	3250.3	91.3
0°-60°	3423.1	96.2
0°-90°	3559.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3559.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4227	
5°	4315	412
15°	4034	1116
25°	2699	1200
35°	827	522
45°	113	88
55°	95	85
65°	74	73
75°	47	49
85°	13	15
90°	0	



TEST NUMBER: P747270

CATALOG NUMBER: LD4D35BD010-EU4DR6020359040-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4227.2
2.5°	4346.0
5°	4314.7
7.5°	4324.6
10°	4316.9
12.5°	4227.7
15°	4033.5
17.5°	3772.8
20°	3459.8
22.5°	3124.7
25°	2698.9
27.5°	2158.7
30°	1744.5
32.5°	1344.5
35°	826.8
37.5°	353.7
40°	125.4
42.5°	115.5
45°	113.3
47.5°	109.5
50°	105.1
52.5°	100.1
55°	95.2
57.5°	90.2
60°	85.3
62.5°	79.8
65°	73.7
67.5°	67.7
70°	61.1
72.5°	53.9
75°	46.8
77.5°	38.5
80°	30.3
82.5°	21.5
85°	12.7
87.5°	4.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)