

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740634

Luminaire Tested: LD4D05D010-EU4DR650210IC9027-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P740634  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D05D010-EU4DR650210IC9027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 465.2 lumens  
Efficiency: N/A  
Efficacy: 62.0 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P740634  
CATALOG NUMBER: LD4D05D010-EU4DR650210IC9027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P740634

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93	93	93													
	2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87	87	87	87	87	87													
	3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80	80	80													
	4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75	75	75													
	5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69	69	69	69	69	69													
	6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65	65	65	65	65	65													
	7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60	60	60	60	60	60													
	8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57	57	57	57	57	57													
	9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53	53	53	53	53	53													
	10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50	50	50	50	50	50													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50052
5°	50090
10°	51856
15°	51942
20°	47823
25°	40748
30°	31188
35°	22035
40°	13008
45°	5269
50°	1921
55°	1067
60°	612
65°	336
70°	351
75°	253
80°	315
85°	251

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5269 cd/sqm



TEST NUMBER: P740634

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9027-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	9.5
10°-20°	127.2	27.3
20°-30°	152.7	32.8
30°-40°	102.6	22.0
40°-50°	30.7	6.6
50°-60°	5.4	1.2
60°-70°	1.5	0.3
70°-80°	0.8	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.0	69.6
0°-40°	426.6	91.7
0°-60°	462.7	99.5
0°-90°	465.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	458	
5°	457	44
15°	459	127
25°	338	153
35°	165	103
45°	34	31
55°	6	5
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P740634

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	458.1
2.5°	460.0
5°	456.7
7.5°	463.6
10°	467.4
12.5°	466.4
15°	459.2
17.5°	441.3
20°	411.3
22.5°	375.9
25°	338.0
27.5°	295.2
30°	247.2
32.5°	203.7
35°	165.2
37.5°	127.1
40°	91.2
42.5°	59.6
45°	34.1
47.5°	18.1
50°	11.3
52.5°	7.8
55°	5.6
57.5°	4.0
60°	2.8
62.5°	1.8
65°	1.3
67.5°	1.1
70°	1.1
72.5°	0.9
75°	0.6
77.5°	0.6
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)