

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740712

Luminaire Tested: LD4D05D010-EU4DR700210IC9027-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P740712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR700210IC9027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 485.2 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740712

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P740712
 CATALOG NUMBER: LD4D05D010-EU4DR700210IC9027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59602
5°	57833
10°	56216
15°	55472
20°	51811
25°	38928
30°	27516
35°	9750
40°	5120
45°	5470
50°	5643
55°	5772
60°	5791
65°	5662
70°	5335
75°	4939
80°	4404
85°	3636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 5796 cd/sqm



TEST NUMBER: P740712

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	10.2
10°-20°	136.4	28.1
20°-30°	150.2	31.0
30°-40°	57.4	11.8
40°-50°	27.1	5.6
50°-60°	27.0	5.6
60°-70°	21.6	4.4
70°-80°	12.4	2.6
80°-90°	3.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.4	69.3
0°-40°	393.8	81.2
0°-60°	447.9	92.3
0°-90°	485.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	485.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	546	
5°	527	50
15°	490	136
25°	323	150
35°	73	57
45°	35	27
55°	30	27
65°	22	22
75°	12	12
85°	3	3
90°	0	



TEST NUMBER: P740712

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	545.5
2.5°	539.8
5°	527.3
7.5°	516.8
10°	506.7
12.5°	498.2
15°	490.4
17.5°	471.9
20°	445.6
22.5°	388.7
25°	322.9
27.5°	281.0
30°	218.1
32.5°	140.9
35°	73.1
37.5°	39.5
40°	35.9
42.5°	35.7
45°	35.4
47.5°	34.5
50°	33.2
52.5°	31.8
55°	30.3
57.5°	28.5
60°	26.5
62.5°	24.3
65°	21.9
67.5°	19.4
70°	16.7
72.5°	14.2
75°	11.7
77.5°	9.2
80°	7.0
82.5°	4.9
85°	2.9
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)