

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748079

Luminaire Tested: LD4D40BD010-EU4DR6540509024-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6540509024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2973.3 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748079
CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P748079

CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157673
5°	157273
10°	157140
15°	152297
20°	138649
25°	120821
30°	100491
35°	79626
40°	57470
45°	36309
50°	18926
55°	10060
60°	5280
65°	2902
70°	1212
75°	1354
80°	942
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36309 cd/sqm



TEST NUMBER: P748079

CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.3	8.6
10°-20°	699.1	23.5
20°-30°	854.6	28.7
30°-40°	693.4	23.3
40°-50°	345.5	11.6
50°-60°	96.4	3.2
60°-70°	21.9	0.7
70°-80°	5.7	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1809.0	60.8
0°-40°	2502.4	84.2
0°-60°	2944.3	99.0
0°-90°	2973.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2973.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2700	
5°	2683	255
15°	2519	699
25°	1875	855
35°	1117	693
45°	440	346
55°	99	96
65°	21	22
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P748079

CATALOG NUMBER: LD4D40BD010-EU4DR6540509024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2699.7
2.5°	2697.7
5°	2682.6
7.5°	2673.9
10°	2649.7
12.5°	2600.5
15°	2518.8
17.5°	2391.0
20°	2230.8
22.5°	2057.8
25°	1874.9
27.5°	1679.3
30°	1490.1
32.5°	1303.2
35°	1116.8
37.5°	930.7
40°	753.8
42.5°	587.9
45°	439.6
47.5°	306.3
50°	208.3
52.5°	143.6
55°	98.8
57.5°	66.6
60°	45.2
62.5°	31.3
65°	21.0
67.5°	10.7
70°	7.1
72.5°	6.7
75°	6.0
77.5°	4.0
80°	2.8
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)