

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740586

Luminaire Tested: LD4D05D010-EU4DR600210IC9035-4LBS1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P740586  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D05D010-EU4DR600210IC9035-4LBS1MW  
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 672.9 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P740586

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9035-4LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P740586  
 CATALOG NUMBER: LD4D05D010-EU4DR600210IC9035-4LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57	
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	73576
5°	73397
10°	75832
15°	75923
20°	69845
25°	59410
30°	45267
35°	32012
40°	18799
45°	7587
50°	2533
55°	1219
60°	503
65°	78
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7587 cd/sqm



TEST NUMBER: P740586

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9035-4LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.6	9.6
10°-20°	185.9	27.6
20°-30°	222.5	33.1
30°-40°	148.8	22.1
40°-50°	44.1	6.6
50°-60°	6.3	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	473.0	70.3
0°-40°	621.8	92.4
0°-60°	672.3	99.9
0°-90°	672.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	672.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	673	
5°	669	65
15°	671	186
25°	493	223
35°	240	149
45°	49	44
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740586

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9035-4LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	673.4
2.5°	672.6
5°	669.2
7.5°	678.3
10°	683.5
12.5°	682.6
15°	671.2
17.5°	644.1
20°	600.7
22.5°	548.7
25°	492.8
27.5°	429.9
30°	358.8
32.5°	295.4
35°	240.0
37.5°	184.5
40°	131.8
42.5°	86.9
45°	49.1
47.5°	25.1
50°	14.9
52.5°	9.6
55°	6.4
57.5°	4.1
60°	2.3
62.5°	1.0
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)