

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748091

Luminaire Tested: LD4D40BD010-EU4DR6540509027-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6540509027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3127.2 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748091

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P748091

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165832
5°	165410
10°	165271
15°	160176
20°	145821
25°	127072
30°	105690
35°	83747
40°	60444
45°	38184
50°	19907
55°	10580
60°	5560
65°	3054
70°	1281
75°	1422
80°	975
85°	871

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38184 cd/sqm



TEST NUMBER: P748091

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.5	8.6
10°-20°	735.3	23.5
20°-30°	898.8	28.7
30°-40°	729.3	23.3
40°-50°	363.4	11.6
50°-60°	101.4	3.2
60°-70°	23.1	0.7
70°-80°	6.0	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1902.6	60.8
0°-40°	2631.9	84.2
0°-60°	3096.6	99.0
0°-90°	3127.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3127.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2839	
5°	2821	269
15°	2649	735
25°	1972	899
35°	1175	729
45°	462	363
55°	104	101
65°	22	23
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P748091

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2839.4
2.5°	2837.3
5°	2821.4
7.5°	2812.2
10°	2786.8
12.5°	2735.1
15°	2649.1
17.5°	2514.8
20°	2346.2
22.5°	2164.3
25°	1971.9
27.5°	1766.2
30°	1567.2
32.5°	1370.7
35°	1174.6
37.5°	978.9
40°	792.8
42.5°	618.4
45°	462.3
47.5°	322.1
50°	219.1
52.5°	151.0
55°	103.9
57.5°	70.1
60°	47.6
62.5°	33.0
65°	22.1
67.5°	11.3
70°	7.5
72.5°	7.1
75°	6.3
77.5°	4.2
80°	2.9
82.5°	2.1
85°	1.3
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)