

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747803

Luminaire Tested: LD4D40BD010-EU4DR4540509035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR4540509035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4088.3 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P747803
CATALOG NUMBER: LD4D40BD010-EU4DR4540509035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P747803

CATALOG NUMBER: LD4D40BD010-EU4DR4540509035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95						95													
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90						90													
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85						85													
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81						81													
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77						77													
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73						73													
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69						69													
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66						66													
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63						63													
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60						60													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	789529
5°	767045
10°	733865
15°	671632
20°	532844
25°	332662
30°	183353
35°	82324
40°	32420
45°	15282
50°	7241
55°	3791
60°	1857
65°	440
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15282 cd/sqm



TEST NUMBER: P747803

CATALOG NUMBER: LD4D40BD010-EU4DR4540509035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	657.1	16.1
10°-20°	1617.3	39.6
20°-30°	1280.7	31.3
30°-40°	426.5	10.4
40°-50°	84.7	2.1
50°-60°	19.2	0.5
60°-70°	2.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3555.1	87.0
0°-40°	3981.6	97.4
0°-60°	4085.4	99.9
0°-90°	4088.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4088.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7226	
5°	6994	657
15°	5938	1617
25°	2759	1281
35°	617	426
45°	99	85
55°	20	19
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747803

CATALOG NUMBER: LD4D40BD010-EU4DR4540509035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7226.1
2.5°	7178.9
5°	6993.6
7.5°	6840.8
10°	6614.6
12.5°	6313.3
15°	5937.6
17.5°	5372.7
20°	4582.7
22.5°	3641.5
25°	2759.4
27.5°	2020.5
30°	1453.3
32.5°	988.4
35°	617.2
37.5°	366.0
40°	227.3
42.5°	149.5
45°	98.9
47.5°	63.7
50°	42.6
52.5°	28.4
55°	19.9
57.5°	13.1
60°	8.5
62.5°	4.5
65°	1.7
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)